

PADICO
ART & CRAFT

Official Site

www.padico.co.jp



English Site

<https://www.padico.co.jp/en/>



Check!

Movie



Video showing how to make an acrylic stand.

Follow me!

SNS



@PADICO_JP



@jewellabyrinth



@padico



@PADICOpadico

PADICO

PADICO HEAD OFFICE : 1-11-11-408 Jinguumae, Shibuya-ku, 150-0001 Tokyo Japan Tel. +81-3-6804-5171

FACTORY : 673-3 Jinba Gotemba, 412-0047, Shizuoka Japan Tel. +81-550-70-7030

©2022 PADICO co.,Ltd. Printed in Japan 403359



New Products

DIY Acrylic Stand with Resin

2022 September
PADICO New Products

PADICO

DIY Acrylic Stand with Resin

Create your custom acrylic stand by sealing your favorite illustrations, anime characters, photos, dried flowers, or anything your fave items.

Make your desk unique and fancy with amazing acrylic stand.



Check!



Video showing how to make an acrylic stand.

New Idea!


Seal your favorite in resin and make the acrylic standee!



What mold do you use?

Place the heat-deformable mold named "Line Mold" on the clear board. Create the desired shape of plates with resin.

→ Go to page 6



What items are sealed in the resin?

Papers & Photographs

Print your favorite image and seal it in the resin. The image enlarged and reduced by a copy machine can be used.

"White Matte Sticker" is recommended for increased visibility.

→ Go to page 10

Masking Tapes and Stickers

Masking tapes with various patterns are good items for resin accessories.

※Please take care not to infringe on copyrights.

Glitter, Dried flowers, Beads, etc.

Mixed into the resin or placed on a part of the resin.

Colorants

Use colorants of UV-LED Resin "Jewel Color" for colored resin and decorate an acrylic stand.


PP films & illustrations printed on PP films

Use "White Matte Sticker" for increased visibility on non-white based papers.

How does an acrylic stand set up straight?

Mount "Stand Joiner" the stand and in the base with resin.

→ Go to page 8



Key Holder



Irregularly shaped imitation agate sliced stone earrings

Accessories



Umbrella Charms



A small rubber band attached to the back side of the resin and use it as an umbrella charm.

Use as markers of bottles.

Acrylic Stand Kit

DIY Resin Acrylic Stand

Starter Kit

with Resin Liquid & UV-LED Lamp



Comes with UV-LED Lamp



A booklet with detailed instructions is also included.

Perfect as a starter kit. Comes with 30g Sun Drop UV-LED Resin

Launch the DIY Resin Acrylic Stand Kit included UV-LED Resin & UV-LED Lamp!

A booklet with detailed instructions is also included. Highly recommended kit as a gift.

Save 12% when you buy a set of these products rather than buying them individually.



Decorate favorite illustrations with embedding parts.

Copied illustration is OK!

Inkjet-printed one is also OK!



※Prepare a separate USB power adapter(DC5.0V≒1.0A)for the light.

Kit Contents

- 1 UV-LED Resin Sun Drop 30g
- 2 UV-LED Handy Light 3
- 3 Clear Board with Thermoplastic Line Mold
- 4 White Matte Sticker
- 5 Stand Joiner (Square Shape Fixed Type)
- 6 Mixing Sticks
- 7 How to Guide in Japanese

Preparations

- Emboss heat gun or dryer
- Photographs or illustrations
- Sealing parts

Launch on September 16th, Friday

DIY Acrylic Stand Kit with Resin

3,200 JPY without tax

#403358

JAN : 4902498733582

Packaging size : W210 x D60 x H290mm
Gross Weight : 240g



Thermoplastic Line Mold & Clear Board

Make resin plates in any shape you like with your own ideas.

The linemold is shaped like a cord and becomes soft and adhesive when heated. Place the heat-deformable mold on the clear board (optional item), create the desired shape of the resin plates in 3mm or 6mm thickness.

3mm thick mold is ideal for accessories

Thick 6mm piece can stand on its own



Line Mold 2 pieces a set
Not actual sizes.



Features of Line Mold

1 Soften the linemold when warmed with an embossing heat gun.

2 The line mold becomes adhesive enough to stick on the clear board.

Prepare an emboss heat gun or a dryer.
Use the clear board sold separately.

3 becomes 3mm or 6mm thick resin molds

4 Cut in half with scissors to make corners.

5 Make an original acrylic stand with "Stand Jointer" sold separately.

Stand Jointer (Square Shape Fixed Type)



Learn more


Free to create resin jewelrys with unique designs.



Resin plates in 2 thicknesses

Thickness of a thin 3mm or a thick 6mm can be made by changing the position of the mold.

3mm thick 6mm thick



Warm up and connect the two into one for the large size resin piece

One linemold is 8 cm long ; two pieces can be adhered together to make a 16 cm length. Large pieces with irregular shapes can be created.



The linemold included with the clear board is a short 12.5 cm product.

Notes

- Line mold must be used on the flat surface of the clear board.
- Use an embossing heat gun or a dryer in low mode for heating linemolds.
- Do not cure resin on the back of the clear board. It will not come off the board.

Recommended Resin : UV-LED Moon Drop Resin, Sun Drop Resin

Launch on September 16th, Friday

Thermoplastic Line Mold 250mm length x 2 pcs

450 JPY without tax

#403349

JAN: 4902498733490

Made in Japan Color/ Clear
Length per pc: W6mmx D3mmx H250mm
Packaging size: W120 x D4 x H185mm
Gross: 18g per bag / Net: 4g per pc
Material: Thermosetting Resin
Operating Temp : 30°C to 50°C



Contents

Thermoplastic Line Mold x 2 pcs

Now Available

Clear Board with Thermoplastic Line Mold


980 JYP without tax

#403348

JAN: 4902498733483

•Clear Board
W100mm x D6mm x H150mm x 1board
•Line Mold(125mm)
W6mm x D3mm x H125mm x 2pcs

The linemold included with the clear board is a short 12.5 cm product.




Stand Jointer

Fixed Type

Specialized parts

to make the resin plate

self-standing



Create your original acrylic standee with the **jointer parts**.




Round Rotating Type

Stand

Base

Recommended Resin: UV-LED Moon Drop Resin, Sun Drop Resin

To make a free-form plate, requires the **clear board** & the **line mold** (sold separately).




When using a line mold, heat it on low with a **hair dryer** or use an **embossing heat gun**.



How to use

For detailed instructions, see the instructions on the back of the package or check QR code for the video.



1 Draw an outline on paper slightly larger than the illustration you wish to seal. Place the clear board on the paper.

2 Form a line mold along the contour of ① and place it so that the two ends of the mold are at the two ends of the stand Part.

3 Pour a thin layer of resin over the entire surface and place the embedded material face down.

Cut excess length with scissors.

Fixed Type

This square shap joint is fixed type.

It is useful for making larger sized stands.

Multiple stands can be made by embedding multiple base parts in the pedestal.

Size

<Stand Part>

<Base Part>



Launch on September 16th, 2022

Line Mold Exclusive Parts
Stand Jointer <Fixed Type>

5sets in 1 bag

240 JPY without tax

#403356

JAN: 4902498733568

Parts size: W16mm x H5mm x D5mm (at joint)
Packaging size: W70mm x H120mm x D12mm
Gross Weight: 3.8g Joint parts: 1.5g
Material: polycarbonates (PC)
Heat Resistance: 120°C / Cool Resistance: -100°C

Patent application in progress



Rotating Type

The round shape joint is rotating type.

Earring stand can be made by setting the round base part into the stand surface.

Multiple stands can be made by embedding multiple base parts in the pedestal.

Size

<Stand Part>

<Base Part>



Launch on September 16th, 2022

Line Mold Exclusive Parts
Stand Jointer <Rotating Type>

5sets in 1 bag


240 JPY without tax

#403357

JAN: 4902498733575

Parts size: W16mm x H5mm x D6mm (at joint)
Packaging size: W70mm x H120mm x D12mm
Gross Weight: 3.3g Joint parts: 1g
Material: polycarbonates (PC)
Heat Resistance: 120°C / Cool Resistance: -100°C

Patent application in progress



White Matte Sticker

Thin paper

can be sealed in resin with a clear picture.

White Matte Sticker is applied to the back of the embedding paper.

The sticker prevents transparency caused by resin seepage and makes the design stand out clearly.

Make the white clear

Resin Seepage Comparison on Copy Paper



without white sticker

with white sticker

Effective on thin paper such as copy paper or masking tape

Resin Seepage Comparison on Masking Tape



without white sticker

with white sticker

Use masking tape patterns for resin accessories.

1

Attach this sticker the back of copy paper or the masking tape.



2

Cut with scissors.



3

Seal in resin.



Clear color



Available Materials

✓ Paper (copy paper and masking tape)

Apply the white sticker on the reverse side of the paper printed with illustrations to improve the clarity of the illustration.


✓ Masking tape and sticker

Apply the white sticker on the reverse side of the masking tape to improve the clarity of the design of the masking tape.

✓ PP Materials such as clear film

Apply the white sticker on the reverse side of the PP film that printed with illustrations to make the design stand out clearly.

White and the design comes out clearly with the white sticker.



without sticker

with sticker

✓ Resin Printable Transfer Sheet

Apply the white sticker on the back of the illustration transferred on the transfer sheet to make the design stand out clearly.

How to Use (when a copy paper is sealed)



Print out the image and make a reduced or enlarged copy of the image to the size you prefer.



Cut the copy paper roughly with scissors.




Cut the white sticker a little larger than the paper in ②.



Peel off the release paper from the white sticker and apply the white one to the back surface of the paper in ②.



Cut the white paper along the picture pattern.



A thin coating of resin before sealing prevents air bubbles.

This is the key to a bubble-free finish.

Resin parts are ready!



This product is not an inkjet printing paper.

Launch on September 16th, 2022

White Matte Sticker

set of 3 sheets

308 JPY without tax

#403355

JAN: 4902498733551

Color: White

Sticker size: W100×H148mm

Packaging size: W120mm×H190mm

Weight: 18g

Material: Sticker PET (White) / Release paper: Paper

Patent application in progress



White Matte Sticker x 3 sheets