

# WEB SITE



[Official Site] www.padico.co.jp New arrivals, product information, etc.



[English Site] https://www.padico.co.jp/en/ Official English Site



[Movie List] https://www.padico.co.jp/movie/

Videos on how to create artworks and use products

SNS





New arrivals, discontinued products, campaigns, and short videos





Instagram dedicated to resin crafts, including works and how to make them





PADICO Official Facebook





Information by fax or email

and how to make your work



PADICO HEAD OFFICE: 1-11-11-408 Jinguumae, Shibuya-ku, 150-0001 Tokyo Japan Tel. +81-3-6804-5171 FACTORY: 673-3 Jinba Gotemba, 412-0047, Shizuoka Japan Tel. +81-550-70-7030




This year's limited edition Jewel Color Sets are the 12-month birthstone color sets.

And now, a new tafrect mold with beautiful brilliance has been developed.

The first molds to be introduced using this technology are 12 small minerals.

Let's create realistic mineral accessories in resin.









# Launch on November 17th, 2023



One product in the birthstone colors of January through June and another in the birthstone colors of July through December, in beautiful transparent clear colors.

































- Set in the birthstone colors of January through June
- Realistic mineral colors reproduced
- Transprent clear color set

Jewel Color Birthstone Color Set <1-6> 1,680 JPY without tax Item #: 403376

JAN: 4902498733766

Common information for all types 1 pc / 6 colors as a set, 3ml each in a bottle / Gross weight: 70g Botte size: 18 mm in a dimeter x 44 mm height / Packaging size: W118 x H136 x D26 mm





Fine nozzle adjusts the amount of liquid to prevent the color from becoming too dark.



Focus on transparency to achieve clear color



Jewel Color Birthstone Color Set <7-12> 1,680 JPY without tax

Realistic mineral colors reproduced

■ Transprent clear color set

Set in the birthstone colors of July through December

Item #: 403377 JAN: 4902498733773



PADICO has developed a plastic material to make resin molds.



# Trial and error by a team of engineers

After many trials and several years of research by engineers, "tafrect" was developed.

# About new plastic material [Tafrect]

In 2023, PADICO developed "Tafrect" a plastic raw material for resin molds.

This fall, we will release "Tafrect Mold," a mold made of this tafrect material.

This mold was finally created in the pursue of the best plastic material for UV-LED resin molds.


The heat resistance temperature, a weak point of previous soft molds, has been increased. Mold softening and whitening caused by heat during resin curing is suppressed. The durability is greatly improved with less deterioration when removed from the mold.

As a special feature, it is now possible to form molds with underparts by injection molding, which was not possible with resins other than silicone.

Compared to silicone molds, production costs and the time can be significantly reduced, resulting in an easy-to-use, beautifully finished mold.

The latest technical process enabled us to make a mold with a shape close to that of the original. More detailed and realistic shapes can be reproduced with molds.

This is the beginning of PADICO's unique and exclusive brand development.



# 5 features of Tafrect Mold

- Beautiful shine as if coated with resin
- Highly resistant to curing heat
- Reduced deterioration and improved durability
- Reproduce complex and realistic shapes
- More resistant to dust than silicone

The first tafrect molds are shapes of minerals. The small sized accessory molds can produce realistic looking minerals.

## features

How to use

1. Pour resin into a mold.

2. Cure the mold under UV-LED lamp.

Common information for all types

Mold size: W60 mm x H40 mm x D12 mm Packaging size: W80 x H138 x D13 mm

Storage condition: Place out of direct sunlight.

Material: Thermoplastic resin

Gross weight: 10g (mold 7g)

1 pc / color:translucent

Made in Japan

- Produces beautiful, shiny, almost real-looking mineral stones
- Design registration pending
- Newly developed resin "tafrect" for improved heat resistance and durability

○ Gently poke the corners of the mold with a stick to spread resin inside the entire mold.

Resins available

2 component epoxy resin

UV-LED resin

3. Allow the mold to cool for 2 to 3 min. before removing it from the mold.

• Leave a gap in the close contact area near the spout for easy removal.

Upper temperature limit: 100~120°C/Cold temperature limit: -20°C

• Easy to remove by adding ethanol for disinfection or resin cleaner.

- Resistant to resin curing heat and does not whiten
- Gives a beautiful finish as if coated with resin Dust and dirt resistant properties compared to silicone molds





high






Please scan this QR cod

to see the 360 degree






# Tafrect Mold <Mineral A>

700 JPY without tax Item #: 403378 JAN: 4902498733780





















# Tafrect Mold < Mineral B>


700 JPY without tax Item #: 403379 JAN: 4902498733797














# Tafrect Mold < Mineral C>


700 JPY without tax Item #: 403380 JAN: 4902498733803







## Mineral D





## Tafrect Mold < Mineral D>

700 JPY without tax Item #: 403381 JAN: 4902498733810





<sup>\* 「</sup>Tafrect」 and 「Tafrect Mold」 are pending trademark registration.

# 1月 Garnet

Deep red, accessories with a strong presence



Birthstone color × Mineral mold

# 2月 Amethyst

Deep purple color, darker even with a single drop Compatible color with fascinating minerals





# 3月 Aquamarine

The clear and gentle sky color is soothing.

# 4月 Morganite









# 8月 Peridot

Beautiful transparent light yellowish green Works well with gold color.



12 \*\*Created by Kimura Premium X( twitter):@k\_i\_m\_u\_r\_a/Instagram:kimurapremium\_works

# Mineral A-c Mineral B-a Mineral A-b 9月 Sapphire Slightly calm tone of blue Can express mineral stones that are not too bright.

# 10月 Green Tourmaline

Deep green color

Thick green is the perfect color for accessories worn by adults.



# 11月 Topaz

Beige with a sense of transparency

It is a basic beige color, but it creates elegant accessories.





# 12月 Tanzanite

Blue-purple in color this accessory has good color and presence.

14 👚 Created by Kimura Premium X(twitter):@k\_i\_m\_u\_r\_a/Instagram:kimurapremium\_works





# Materials/Tools

- UV-LED Resin Star Drop Hard
- Jewel Color Birthstone Color Set <1-6>
- Tafrect Mold <Mineral D> Eyebolts

Eye pins

Pin Vise

Pliers

Nippers

Tweezers

- UV-LED Lamp
- Handy Heater
- Mixing Palette
- Mixing Stick
- Shading Case
- Resin Cleaner
- (ethanol diluted 2x with water) Permanent maker pen<Gold>
- Straight pipe accessory parts





Put 3 drops of emerald green Mix it well with a stick. into star drop resin.





air bubbles.



Use a handy heater to remove Place in a case to prevent Pour the green resin into the Cure it under UV-LED lamp. exposed to light and cool it mineral D-a mold.







the cleaner between the mold and the resin to make it easier to remove.



Cool it down first, then soak Use a pin vise to make a hole.



Put resin on the eyebolt and Paint the top of the part with insert it into the drilled hole to a gold pen and let it dry. cure and adhere by light.





Connect the parts through 9 pins in a straight pipe.



Connect earrings and fittings.

# Tanzanite colored mineral necklace The blue-purple color is exquisite and attractive. Simple but cute accessory in combination with clear. Created by Kimura Premium X(twitter ):@k\_i\_m\_u\_r\_a / Instagram:kimurapremium\_works



# Materials/Tools

- UV-LED Resin Star Drop Hard
- Jewel Color Birthstone Color Set <7-12>
- ●Tafrect Mold <Mineral D>
- UV-LED Lamp
- Handy Heater Mixing Palette
- T pins Eye pins Jump rings Pin Vise

Tweezers

Nippers

- Mixing Stick
- Shading Case
- Resin Cleaner
- (ethanol diluted 2x with water) Pliers
- Pearl beads
- Neck chain











Use a handy heater to remove air bubbles.



exposed to light and cool it mineral D-a mold.





Place in a case to prevent Pour the green resin into the Cure it under UV-LED lamp.



the cleaner between the mold clear color resin. and the resin to make it easier to remove.



Cool it down first, then soak Make a same shaped ore with



Fasten the pearl beads Drill holes in the same position Pass 9 pin through the hole Connect the stone to the neck through T-pins.



in the two stones.



and round the tip. Then, attach chain with a jump ring. a pearl to it with a jump ring.




Iewel Color Mixing Palette for colored resin has been renewed. Palettes for making large quantities of colored resins are now available in three sizes.

## features

- The size-S can contain up to 10g of resin, the size-M up to 30g, and the size-L up to 60g.
- This palette has a scale for liquid volume.
- Holder can be used for color mixing pan.
- Unlike silicone, this palette is dust resistant.

\*The scale is for reference only and varies depending on the specific gravity of the liquid. \*When keeping resin in the palette, cover the entire palette with aluminum foil to shade.

Design registration pending Utility model registration pending



Resin spout

Lsize

The shape is designed diagonally



# Jewel Color Mixing Palette < S size >

Storage condition: Place out of direct sunlight. / Made in Japan

400 JPY without tax Item #: 403382 JAN: 4902498733827 3 palettes in a set

Common information for all types

Palette weight: 1.7g Palette size: W73×H52×D20mm Packaging size: W90×H150×D21mm



1 pc / color: semi-transparent / material: PP / Upper temperature limit: 80°C / Cold temperature limit: -20°C

# Jewel Color Mixing Palette < M size >

400 JPY without tax Item #: 403383 JAN: 4902498733834 2 palettes in a set Palette weight: 2.5g

Palette size: W90×H64×D27mm

Packaging size: W111×H160×D28mm

Up to 30g

M size

400 JPY without tax Item #: 403384

JAN: 4902498733841 2 palettes in a set

Palette weight: 4.7g Palette size: W114×H80×D34mm Packaging size: W131×H180×D35mm

Jewel Color Mixing Palette < L size >

The size closest to the existing pallet is size S.

# Existing pallet sizes will be discontinued while stocks last.

New stir stick that prevents air bubbles is released.

## features

- Can mix colors quickly.
- Unique design shape prevents air bubbles.
- Has a spatula to scrape out resin.

Mix with a normal

shaped mixing stick

Design registration pending

Utility model registration pending

\*There are bubbles in the handle due to product formation, but this does not affect the strength of the product.

# Quickly mixes resin and colorants.

Good for mixing



Two specially shaped sticks prevent air bubbles when mixing the resin.

Mix with Stir Stick

### Unique design shape reduces air bubbles! Stir Stick

<Use the back end as spatula>

400 JPY without tax

Storage condition: Place out of direct sunlight.



easy to quickly mix and remove resin out.



Item #: 403385 JAN: 4902498733858

Stick weight: 4.5g Stick size: W15×H160×D7mm Packaging size: W60×H232×D8mm

Color: Clear / material: thermoplastic resin Upper temperature limit: 80°C Cold temperature limit: -20°C

Made in Japan



\*Photo is not full size.

Stir Stick

[Side]

[Front]

# Scheduled to be launched in January 2024


18 LEDs, large size and powerful lamp, ideal for resin.

## features

- 18 UV-LEDs, cures resin evenly and firmly.
- Hybrid curing unit, compatible for LED 405nm & 365 nm.
- The light's beam coverage is approximately 4 times wider than that of a handy light and can be used for large molds.
- 18 mm thin tablet type for convenient storage.
- Can be used stationary with a retractable stand.
- Has automatic 30 seconds and 60 seconds timer.

\*Because LED light emits yellow light unlike normal blue light, so the light may be perceived as strong.

O Press the button once to turn it into a 30 seconds timer, press it twice to 60 second timer, and three times to turn the timer off.





A separate DC5V \= 2.1A USB power adapter or mobile battery with USB-A port output terminal is required.

\*DC5.0V≒1A power adapter may result in uncured due to insufficient power. \*Not compatible with power supply from PC, and PD charger and some high-speed chargers.

O UV Resin Compatible Resins UV-LED Resin



LED Lights Wavelength 18 LEDs 405nm+365nm Power Supply DC5V≒2.1A~3.0A Varies depending on the power adapter

26

ABS, PC Timing function 30/60 seconds White Unit color Main unit weight 220g

Packaging size W170×H265×D25mm W229×H136×D18mm Unit size Irradiation area W210mm×D140×H50mm (Max. stand height: 58mm)

